

## Product data sheet

### Characteristics

# 30USMHW-WE

## UNIVERSAL ROCKER SWITCH MECH

### MARKED HWS 1/2W 20 A16 AX - WHITE

## ELECTRIC



#### Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

#### Complementary

Switch function	2-way 1-way
Number of rocker	1
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A 16 AX, fluorescent lamp
Marking	Hot
Marking location	Marking on surface
Actuator	Rocker

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	14.0 g
Package 1 Height	3.1 cm
Package 1 width	2.4 cm
Package 1 Length	2.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.082 kg
Package 2 Height	3.6 cm
Package 2 width	5 cm
Package 2 Length	7.4 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	500.0 kg
Package 3 Height	22.6 cm

Package 3 width	19.1 cm
Package 3 Length	35.9 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>