

## Product data sheet

### Characteristics

# 3105SPF3

Clipsal Actassi, Terrestrial Splitter, 3 Way, F-Type, Terrestrial, 1 Leg Power Pass, 1GHz



### Main

Product brand	Clipsal
Range of product	Electricimagination
Product or component type	Splitter block
Number of terminals	1 earth contact





### Complementary

Connections - terminals	F connection
Transmission frequency	5...1000 MHz
Maximum splitter loss	6.3 dB
Number of outputs	3
Number of inputs	1
Number of mounting holes	2

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	11.0 cm
Package 1 Length	12.5 cm
Package 1 Weight	0.06 kg

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes