

Product data sheet

Characteristics

3044HA-VW

Clipsal Iconic, 4 switches, horizontal, 10 A, vivid white



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Horizontal
Switch function	1-pole 1/2-way
Number of rocker	4
Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Height	78 mm
Width	120 mm
Depth	39 mm
Net weight	0.124 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.6 cm
Package 1 Length	14.3 cm
Package 1 Weight	131 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	328 cm
Package 2 Width	106 cm
Package 2 Length	146 cm
Package 2 Weight	1414 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile