

## Product data sheet

### Characteristics

# 39MUOD-WE

## Switch Mechanism, Clipsal - Mechanisms, 3 Pos Up / Off / Down



### Main

Range of product	Standard Series Series 30
Product brand	Clipsal
Assembly Type	Basic element

### Complementary

Control type	Rotary knob
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Load type	Fluorescent lamp 10 A LEDi lamp 100 W
Marking	UP-OFF-DOWN
Marking location	Marking on surface

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	2.2 cm
Package 1 Length	3.2 cm
Package 1 Weight	15.2 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4 cm
Package 2 Width	5.8 cm
Package 2 Length	11.6 cm
Package 2 Weight	150 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	10.2 cm
Package 3 Width	12 cm
Package 3 Length	17 cm
Package 3 Weight	700 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations