

Product data sheet

Characteristics

3044VAG

Clipsal Iconic, Gridplate and Mechanism, 4 Gang, 250V, 10AX



Main

Range of product	Iconic
Range of product	Clipsal Iconic
Aesthetic name	Iconic
Product or component type	Switch Switch
Product brand	Clipsal
Device application	Switching loads
Device presentation	Complete product
Provided equipment	Switch
Colour	White (-)
Type of packing	Bag
Quantity per set	1
Sale per indivisible quantity	1
Motor M-rating AS3133	M80
Load type	Fluorescent 10 AX LED lamp 100 W

Complementary

Technology type	Electromechanical
Switch pattern	[4]
Switch application	On/off switching
Device mounting	Flush
Switch function	1-pole 1/2-way
[Ue] rated operational voltage	230/240 V
Number of modules	4 modules
Number of gangs	4 gangs
Number of rocker	4
Actuator	Rocker
Product destination	Rocker switch
Range compatibility	Iconic
Connections - terminals	Screw terminal
Surface treatment	Plastic coated
Rated current	10 AX at 230/240 V AC
Local signalling	Without light indicator
Material	Plastic: rocker
Height	120 mm
Width	78 mm
Depth	39 mm

Environment

Standards	AS/NZS 3133
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.1 cm
Package 1 Length	11.5 cm
Package 1 Weight	0.106 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations