

Product data sheet

Characteristics

30CSFM-WE

Clipsal - Mechanisms, Fan Speed Controller, 240V, 75VA, Series 30



Main

Range of product	Series 30CSFM
Product brand	Clipsal
Device presentation	Basic element
Load type	Capacitive

Complementary

Power consumption in VA	75 VA
Network frequency	50 Hz
Mounting support	Wall

Environment

Standards	AS/NZS CISPR 15:2002
-----------	----------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.9 cm
Package 1 Length	8.3 cm
Package 1 Weight	54 g
Unit Type of Package 2	CAR
Number of Units in Package 2	250
Package 2 Height	26 cm
Package 2 Width	37 cm
Package 2 Length	50 cm
Package 2 Weight	17209.25 g
Unit Type of Package 3	PAL
Number of Units in Package 3	2000
Package 3 Height	120 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	34428500 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information