

Product data sheet

Characteristics

30MD2-WE

Switch 30 Series Mechanism - Double-pole -
2 way - Double throw - 250 V - 10 A - White
Electric



Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Device presentation	Basic element

Complementary

Switch function	2-way
Actuator	Rocker
Number of rocker	1
Number of poles	2
Device mounting	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	22 g
Package 1 Height	22 mm
Package 1 width	25 mm
Package 1 Length	35 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.134 kg
Package 2 Height	48 mm
Package 2 width	66 mm
Package 2 Length	94 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	5.6 kg
Package 3 Height	237 mm
Package 3 width	203 mm
Package 3 Length	300 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile