



Main

Range of product	Clipsal Iconic
Product brand	Clipsal
Product or component type	Movement detector
Function of module	Motion detection
Device application	Power circuit application Lighting
Sensor type	PIR

Complementary

Provided equipment	Carrier (plastic) Finishing accessory
[Ue] rated operational voltage	220/240 V AC 50 Hz 25 °C
Power consumption in W	1 W at 240 V AC 50 Hz
Maximum load current	3 A for per output
Rated power in W	100 W LED lighting 750 W incandescent 100 W fluorescent 400 W LV halogen 100 W motor
Protection type	Input surge protection for sensor
Electrical insulation class	Double insulation
Type of setting	Time adjustment: 20...900 s
Light intensity adjustment	10...2000 lux
Movement detection area	5 m
Detection angle	100° horizontal 82° vertical
Material	Plastic
Device mounting	Wall mounted
Mounting height	1.2 m
Type of installation	Indoor installation
Width	48.5 mm
Height	23.5 mm
Depth	49 mm
Embedding depth	41 mm

Environment

IP degree of protection	IP20 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-10...50 °C
Ambient air temperature for storage	-20...60 °C
Relative humidity	5...90 % non-condensing
Standards	AS/NZS 60669.2.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	6.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	78.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information