

Product data sheet

Characteristics

30PB-WE

Impress Series, Push Button Switch, 20A, Series 30



Main

Range of product	Series 30 Impress
Product or component type	Push-button
Colour	White electric
Product brand	Clipsal
Device presentation	Basic element

Complementary

Colour code	WE
Actuator	Push-button
Local signalling	Without light indicator
Material	Plastic
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Depth	10 mm
Width	21 mm
Length	21 mm
Load type	Fluorescent 20 A LEDi lamp 250 W

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	2.8 cm
Package 1 Length	7 cm
Package 1 Weight	22 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.