


Product data sheet

Characteristics

30RJ45SMA5SHC-WE

Clipsal Actassi, RJ45 Jack, CAT5E UTP 30M
Shutter



Main

Range	Actassi
Product name	Actassi S-110
Product type	RJ45 connector
Device presentation	Two piece design
Colour tint	Connector housing: white (ABS + PC) Shutter: white (ABS + PC) Top cover: transparent (PC) IDC cover: green (PC)
Wiring Colour configuration	TIA-568A/B
Quantity per set	Set of 1

Complementary

[In] rated current	1.5 A at 25 °C
Voltage proof	1000 V AC/DC peak, between contacts
Contact resistance	20 mOhm
Insulation resistance	Initial insulation resistance: ≥ 500 MOhm at 100 V DC
AWG gauge	AWG 24...AWG 23
Durability	750 cycles
Contact pins	8 pins of copper alloy and gold plated conforming to IEC 60603-7
Tool type	Punch down tool Quick termination tool
Cable outer diameter	0.9...1.4 mm
Compatible LAN cable types	UTP
Communication network category	5e
Supported applications	1000BASE-T
Connections - terminals	Insulation displacement contact
Transmission frequency	1...100 MHz
Type of footprint	S-110 30 mech
Height	0.02 M 22 mm
Length	0.04 M 36 mm
Width	0.02 M 16 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.





Environment

Operational temperature range	-10...60 °C -10...60 °C
Ambient air temperature for storage	-40...70 °C -40...70 °C
Climatic category	40/070/21 (21 days)
Flame retardance	UL94-V0 conforming to UL listed
Product certifications	UL listed
Standards	ANSI/TIA-568-C.2 IEC 60603-7-2 ISO/IEC 11801:2011 Ed.2.2 AS/NZS 3080:2003 UL 1863 IEC 60512-99-001 IEC 60512-99-002

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	10.5 cm
Package 1 Length	15 cm
Package 1 Weight	9.4 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	13 cm
Package 2 Width	13 cm
Package 2 Length	18 cm
Package 2 Weight	262 g
Unit Type of Package 3	S03
Number of Units in Package 3	160
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2579 g

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------