

Product data sheet

Characteristics

3105RG6Q3RF

CABLE RG6 QUADSHLD FLOOD 305M



Main

Product brand	Clipsal
Sheath type	Foil + braiding
Colour	External sheath: black

Complementary

Diameter	Conductor: inner: 1.02 mm Conductor: external: 4.57 mm
Material	Inside bare copper conductor Outside aluminium conductor
Cable stiffness	Solid class 1
Cable insulation material	PE (polyethylene) PVC (polyvinyl chloride)
External diameter	7.57 mm
AWG gauge	AWG 18

Environment

Ambient air temperature for operation	80 °C
---------------------------------------	-------

Packing Units

Package 1 Weight	13627.000 g
Package 1 Height	285.000 mm
Package 1 width	365.000 mm
Package 1 Length	365.000 mm

Offer Sustainability

EU RoHS Directive	Not compliant
-------------------	---------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.