

## Product data sheet

### Characteristics

# 31100

ComPact, Switch disconnecter, Compact  
INS250-100 , 100 A, standard version with  
black rotary handle, 3 poles



### Main

Range	ComPact
Product or component type	Switch disconnecter
Product name	ComPacT INS
Poles description	3P
Network type	AC DC
Network frequency	50/60 Hz
[Ie] rated operational current	AC-22A: 100 A AC 50/60 Hz 220/240 V AC-22A: 100 A AC 50/60 Hz 380/415 V AC-22A: 100 A AC 50/60 Hz 440/480 V AC-22A: 100 A AC 50/60 Hz 480 V NEMA AC-22A: 100 A AC 50/60 Hz 500/525 V AC-22A: 100 A AC 50/60 Hz 660/690 V AC-23A: 100 A AC 50/60 Hz 220/240 V AC-23A: 100 A AC 50/60 Hz 380/415 V AC-23A: 100 A AC 50/60 Hz 440/480 V AC-23A: 100 A AC 50/60 Hz 480 V NEMA AC-23A: 100 A AC 50/60 Hz 500/525 V AC-23A: 100 A AC 50/60 Hz 660/690 V DC-22A: 100 A DC 125 V 2 poles in series DC-23A: 100 A DC 125 V 2 poles in series
[Ui] rated insulation voltage	750 V AC 50/60 Hz
[Ith] conventional free air thermal current	100 A at 60 °C
[Icm] rated short-circuit making capacity	30 kA switch-disconnector alone 690 V AC at 50/60 Hz 330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz
[Ue] rated operational voltage	125 V DC 690 V AC 50/60 Hz
Suitability for isolation	Yes
Contact position indicator	Yes
Visible break	No
Pollution degree	3

### Complementary

Control type	Direct front rotary handle
Handle colour	Black
Mounting mode	Fixed
Mounting support	Rail Plate
Upside connection	Front
Downside connection	Front

Maximum power	AC-23: 22 kW at 220/240 V AC 50/60 Hz AC-23: 22 kW at 230 V AC 50/60 Hz (NEMA) AC-23: 45 kW at 380/415 V AC 50/60 Hz AC-23: 55 kW at 440 V AC 50/60 Hz AC-23: 55 kW at 480 V AC 50/60 Hz (NEMA) AC-23: 55 kW at 500/525 V AC 50/60 Hz AC-23: 55 kW at 660/690 V AC 50/60 Hz
Rated duty	Uninterrupted
[I <sub>cw</sub> ] rated short-time withstand current	1.8 kA during 30 s conforming to IEC 60947-3 2.2 kA during 20 s conforming to IEC 60947-3 4.9 kA during 3 s conforming to IEC 60947-3 8.5 kA during 1 s conforming to IEC 60947-3
Mechanical durability	15000 cycles
Electrical durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz DC-22A: 1500 cycles 125 V DC 2 poles in series DC-23A: 1500 cycles 125 V DC 2 poles in series
Connection pitch	35 mm
Height	136 mm
Width	140 mm
Depth	96 mm
Net weight	2 kg

## Environment

Standards	IEC 60947-1 IEC 60947-3
Product certifications	CCC[RETURN]KEMA-KEUR
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.8 cm
Package 1 Width	16.5 cm
Package 1 Length	17.0 cm
Package 1 Weight	2.235 kg
Unit Type of Package 2	S04
Number of Units in Package 2	9
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	20.953 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Contractual warranty</b>	
Warranty	18 months