

Product data sheet

Characteristics

31E2RUDM-WE

DIMMER MECHANISM ISRC 350W



Main

Range of product	Series 30 C-Thru
Product brand	Clipsal
Device presentation	Basic element
Dimmer type	Universal
Colour	White electric

Complementary

Power consumption in W	350 W
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Control type	Rotary knob
Mounting support	Wall

Environment

Standards	AS/NZS 3100 IEC 60669-2-1 AS/NZS CISPR 15 IEC 61000-3-2
-----------	--

Packing Units

Package 1 Weight	44.000 g
Package 1 Height	30.000 mm
Package 1 width	90.000 mm
Package 1 Length	160.000 mm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.