

## Product data sheet

### Characteristics

# 4CB120/6DC

Miniature circuit breaker, MAX4, 1P, 20 A, C curve, 6000 A, 250 V



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Curve code	C
Number of poles	1
[In] rated current	20 A
Number of modules	1
[Ue] rated operational voltage	250 V
Breaking capacity	6 kA conforming to IEC 60947-2
Network type	DC
[Uimp] rated impulse withstand voltage	6 kV
Mechanical durability	20000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 1...25 mm <sup>2</sup> rigid Screw terminal for 1 cable(s) 1...16 mm <sup>2</sup> flexible Screw terminal for 1 cable(s) 1...16 mm <sup>2</sup> flexible with ferrule
Wire stripping length	14 mm
Tightening torque	2.5 N.m

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Standards	AS/NZS 60898
Pollution degree	3
Relative humidity	95 % at 55 °C
Height	81 mm
Width	18 mm
Depth	78.5 mm
Net weight	128 g

### Packing Units

Package 1 Weight	115.000 g
Package 1 Height	72.000 mm
Package 1 width	85.000 mm
Package 1 Length	20.000 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>