

Product data sheet

Characteristics

32ELEDM2-WE

30 Series, Rotary LED Dimmer Module, 150W,
220-240V AC



Main

Range	30 Series
Product or component type	Dimmer
Device presentation	Mechanism
Dimmer type	Trailing edge
Colour tint	White electric (WE)
Type of packing	Box
Load type	Dimmable LED - 150 W Incandescent - 150 W

Complementary

Range compatibility	Clipsal
Fixing mode	Clip-in
Surface finish	Glossy
Ambient air temperature for storage	0...60 °C
Dimmer control	Rotary
[Ue] rated operational voltage	220...240 V AC 50 Hz 150 W
Function available	Brightness adjustment
Protection type	Short-circuit Overload protection Thermal protection
Ambient air temperature for operation	0...45 °C
Relative humidity	5...90 %
Connections - terminals	2-wire supply
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	22.84 mm
Width	22.84 mm
Depth	54.7 mm
Embedding depth	39 mm

Environment

Standards	AS/NZS 60669.2.1
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	7.8 cm
Package 1 Length	9.5 cm
Package 1 Weight	57.0 g

Unit Type of Package 2	PAL
Number of Units in Package 2	2304
Package 2 Height	105.0 cm
Package 2 Width	114.0 cm
Package 2 Length	114.0 cm
Package 2 Weight	192.0 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	48
Package 3 Height	22.7 cm
Package 3 Width	26.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	3.67 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information