

Product data sheet

Characteristics

40USM

Clipsal Iconic, switch, mechanism, 1 or 2-way,
20 A / 16 AX



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Mechanism
Control type	Rocker
Switch function	1-pole 1/2-way
Rated current	20 A
[Ue] rated operational voltage	250 V
Material	Plastic
Connections - terminals	Screw terminal
Height	23 mm
Width	23 mm
Depth	32 mm
Net weight	0.016 kg

Packing Units

Package 1 Weight	16.000 g
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.