

## Product data sheet

### Characteristics

# 41E350PBT2SM-VW

Clipsal Iconic - timer -pushbutton - 350 W - 2 wires - ControlLink



### Main

Range	Clipsal Iconic
Product or component type	Timer
Device presentation	Mechanism

### Complementary

Device mounting	Flush
Actuator	Push-button
Fixing mode	Locking bar
Colour tint	Vivid white
Surface finish	Matt
Type of packing	Box
Sale per indivisible quantity	1
Type of operator	Momentary
Time delay	30 s 1 min 5 min 15 minutes 30 minutes 1 h 2 h 4 h
Remote control type	Push-button
[Ue] rated operational voltage	240 V AC 50 Hz
Load type	Incandescent lamp 350 W Medium voltage halogen lamp 350 W Low voltage halogen lamp with iron core transformer 350 W Linear fluorescent ballast 250 W Compact fluorescent load 250 W Dimmable LED lighting driver 350 W LED lighting driver (non-dimmable) 250 W Resistive 350 W
Power range	> 10 W
Derating factor	1 devices(350 W) without derating 2 devices(250 W) with derating factor 3 devices(220 W) with derating factor 4 devices(175 W) with derating factor 5 devices(120 W) with derating factor 6 devices(100 W) with derating factor
Operating distance	30 m
Control signal type	ControlLink
Connections - terminals	Screw terminals
Number of terminals	3

Wiring configuration	2-wire
Screwdriver shape	Philips Square drive no 1 (SQ1)
Local signalling	LED indicator (warm white)
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	23.5 mm
Width	23.5 mm
Depth	42 mm
Embedding depth	39 mm
Standards	AS/NZS 60669.2.1

## Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	0...90 %

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	67.0 g
Package 1 Height	4.1 cm
Package 1 width	6.9 cm
Package 1 Length	8.7 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>