

## Product data sheet

### Characteristics

# 4CB304/6

Clipsal - Max 4, Miniature Circuit Breakers, 3 Pole, 3 Modules, 54mm, 415V, 4A, 6Ka

### Main

Product brand	Clipsal
---------------	---------

### Complementary

Curve code	C
Number of poles	3
[In] rated current	4 A
Number of modules	3
[Ue] rated operational voltage	415 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz
[Ui] rated insulation voltage	440 V
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 0.75...16 mm <sup>2</sup> rigid Screw terminal for 1 cable(s) 0.33...10 mm <sup>2</sup> flexible Screw terminal for 1 cable(s) 0.33...10 mm <sup>2</sup> flexible with ferrule
Wire stripping length	13 mm
Tightening torque	2 N.m

### Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Standards	AS/NZS 60898
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Height	81 mm
Width	54 mm
Depth	78.5 mm
Net weight	310 g

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	5.3 cm
Package 1 Length	8.5 cm
Package 1 Weight	319 g

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>