

## Product data sheet

### Characteristics

## 4CB125/6

Clipsal MAX4, Miniature circuit breaker 1P 25 A  
C curve 6000 A 240 V



### Main

Product brand	Clipsal
---------------	---------

### Complementary

Curve code	C
Number of poles	1
[In] rated current	25 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz
[Ui] rated insulation voltage	440 V
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 0.75...16 mm <sup>2</sup> rigid Screw terminal for 1 cable(s) 0.33...10 mm <sup>2</sup> flexible Screw terminal for 1 cable(s) 0.33...10 mm <sup>2</sup> flexible with ferrule
Wire stripping length	13 mm
Tightening torque	2 N.m





### Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Standards	AS/NZS 60898
Tropicalisation	2
Relative humidity	95 % at 55 °C
Height	81 mm
Width	18 mm
Depth	78.5 mm
Net weight	115 g

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	107.8 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	7 cm
Package 2 Width	8.4 cm
Package 2 Length	23 cm
Package 2 Weight	1.36 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>