

Product data sheet

Characteristics

4RC240SI30

Clipsal MAX4, Residual current circuit breaker
2P 40 A 30 mA type A-SI 240 V



Main

Range	MAX4
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	40 A
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A-SI (Super Immunised)

Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	6 kV
Mounting support	DIN rail
Size	81 x 72 x 75 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61008
IP degree of protection	IP40
Pollution degree	2
Ambient air temperature for operation	-5...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	9.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	213 g
Unit Type of Package 2	S03
Number of Units in Package 2	54
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.932 kg
Unit Type of Package 3	P12
Number of Units in Package 3	432
Package 3 Height	44.4 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	107.458 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations