

Product data sheet

Characteristics

4RC240SI30

Residual current circuit breaker, MAX4, 2P, 40 A, 30 mA, type A-SI, 240 V



Main

| | |
|--------------------------------|---|
| Range | MAX4 |
| Product or component type | Residual current circuit breaker (RCCB) |
| Product brand | Clipsal |
| Poles description | 2P |
| Number of modules | 2 |
| [In] rated current | 40 A |
| Earth-leakage sensitivity | 30 mA |
| Earth-leakage protection class | Type A-SI (Super Immunised) |

Complementary

| | |
|--|---|
| [Ue] rated operational voltage | 240 V AC |
| [Uimp] rated impulse withstand voltage | 6 kV |
| Mounting support | DIN rail |
| Size | 81 x 72 x 75 mm conforming to DIN 43880 |


Environment

| | |
|---------------------------------------|--------------|
| Standards | AS/NZS 61008 |
| IP degree of protection | IP40 |
| Pollution degree | 2 |
| Ambient air temperature for operation | -5...40 °C |

Packing Units

| | |
|------------------|-----------|
| Package 1 Weight | 212.800 g |
| Package 1 Height | 82.000 mm |
| Package 1 width | 90.000 mm |
| Package 1 Length | 40.000 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |