

Product data sheet

Characteristics

4CB150D10

Clipsal - Max 4, Miniature Circuit Breakers, 1.5 Module, 1 Pole, 50A, 10kA



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	D
Number of poles	1
[In] rated current	50 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	10 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz
[Ui] rated insulation voltage	500 V
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 0.5...35 mm ² rigid Screw terminal for 1 cable(s) 0.5...25 mm ² flexible Screw terminal for 1 cable(s) 0.5...25 mm ² flexible with ferrule
Wire stripping length	13 mm
Tightening torque	3.5 N.m

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Standards	AS/NZS 60898
Tropicalisation	2
Relative humidity	95 % at 55 °C
Height	81 mm
Width	18 mm
Depth	78.5 mm
Net weight	115 g

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	119 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes