

## Product data sheet

### Characteristics

# 4RC463SI30

Clipsal MAX4, Residual current circuit breaker  
4P 63 A 30 mA type A-SI 415 V



### Main

Range	MAX4
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Poles description	4P
Number of modules	4
[In] rated current	63 A
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A-SI (Super Immunised)

### Complementary

[Ue] rated operational voltage	415 V AC
[Uimp] rated impulse withstand voltage	6 kV
Mounting support	DIN rail
Size	81 x 72 x 75 mm conforming to DIN 43880

### Environment

Standards	AS/NZS 61008
IP degree of protection	IP40
Pollution degree	2
Ambient air temperature for operation	-5...40 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.5 cm
Package 1 Length	8.0 cm
Package 1 Weight	393.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations