

Product data sheet

Characteristics

4RC463SIS300

Residual current circuit breaker, MAX4, 4P, 63 A, 300 mA, type A-SI, 415 V



Main

Range	MAX4
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Poles description	4P
Number of modules	4
[I _n] rated current	63 A
Earth-leakage sensitivity	300 mA
Earth-leakage protection class	Type A-SI (Super Immunised)

Complementary

[U _e] rated operational voltage	415 V AC
[U _{imp}] rated impulse withstand voltage	6 kV
Mounting support	DIN rail
Size	81 x 72 x 75 mm conforming to DIN 43880
Trip unit protection functions	Selective protection

Environment

Standards	AS/NZS 61008
IP degree of protection	IP40
Pollution degree	2
Ambient air temperature for operation	-5...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.35 kg
Package 1 Height	9.2 cm
Package 1 width	7.7 cm
Package 1 Length	8.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	1
Package 2 Weight	1.1 kg
Package 2 Height	9 cm
Package 2 width	11 cm
Package 2 Length	26 cm
Unit Type of Package 3	S03
Number of Units in Package 3	27
Package 3 Weight	9.937 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins