

Product data sheet

Characteristics

4RCBE232/30S

Clipsal MAX4, RCBO SLIM 1PN 32A C curve
30mA Type A 6000A



Main

| | |
|--------------------------------|---|
| Range | MAX4 |
| Product or component type | Residual current breaker with overcurrent protection (RCBO) |
| Product brand | Clipsal |
| Device application | Distribution |
| Poles description | 1P + N |
| Neutral position | Left |
| Number of modules | 1 |
| Number of protected poles | 1 |
| [In] rated current | 32 A |
| Network type | AC |
| Trip unit technology | Thermal-magnetic |
| Curve code | C |
| Earth-leakage sensitivity | 30 mA |
| Earth-leakage protection class | Type A |
| Breaking capacity | 6000 A |

Complementary

| | |
|--------------------------------|-------------------|
| [Ue] rated operational voltage | 240 V AC |
| Local signalling | ON/OFF indication |
| Mounting mode | Clip-on |
| Mounting support | DIN rail |


Environment

| | |
|-------------------------|--|
| IP degree of protection | IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529 |
|-------------------------|--|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.02 cm |
| Package 1 Width | 0.075 cm |
| Package 1 Length | 0.1 cm |
| Package 1 Weight | 0.156 kg |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| Sustainable packaging | Yes |

| | |
|----------------------------|---|
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |