

Product data sheet

Characteristics

4RCBE232S110

Residual current breaker with overcurrent protection (RCBO), MAX4, 1P + N, 32 A, C curve, 6000 A, 110 V, 30 mA, A type



Main

Range	Clipsal - Series 4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Device application	Distribution
Poles description	1P + N
Neutral position	Left
Number of modules	1
Number of protected poles	1
[In] rated current	32 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A
Breaking capacity	6 kA

Complementary

[Ue] rated operational voltage	110 V AC
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
-------------------------	--

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	0.002 cm
Package 1 Width	0.008 cm
Package 1 Length	0.01 cm
Package 1 Weight	0.141 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins