

Product data sheet

Characteristics

4CB240/6DC

Miniature circuit breaker, Clipsal - Max 4, DC
 Network type 2P 40 A C curve 6000 A 500 V



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	C
Number of poles	2
[In] rated current	40 A
Number of modules	2
[Ue] rated operational voltage	500 V
Breaking capacity	6 kA conforming to IEC 60947-2
Network type	DC
[Uimp] rated impulse withstand voltage	6 kV
[Ui] rated insulation voltage	500 V
Mechanical durability	20000 cycles
Connections - terminals	Screw terminal for 1 cable(s) 1...35 mm ² rigid Screw terminal for 1 cable(s) 1...25 mm ² flexible Screw terminal for 1 cable(s) 1...25 mm ² flexible with ferrule
Wire stripping length	14 mm
Tightening torque	3.5 N.m

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Standards	AS/NZS 60898
Pollution degree	3
Relative humidity	95 % at 55 °C
Height	81 mm
Width	36 mm
Depth	78.5 mm
Net weight	256 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	8.5 cm
Package 1 Length	3.6 cm
Package 1 Weight	243.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations