

## Product data sheet

### Characteristics

# 4RCBM225/30

Residual current breaker with overcurrent protection (RCBO), MAX4, 2P, 25A, C curve, 6000A, AC type, 30mA



#### Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	25 A
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type AC
Breaking capacity	6000 A

#### Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880





#### Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.4 cm
Package 1 Width	10.3 cm
Package 1 Length	4.2 cm
Package 1 Weight	228.0 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Halogen content performance	Halogen free plastic parts product