

## Product data sheet

### Characteristics

# 5085EDLB-PW

Wall Plate, C-Bus eDLT, Saturn, Enhanced Dynamic Labelling Technology, 5 Key Grid



#### Main

Range	C-Bus
Product brand	Clipsal
Product name	C-Bus Saturn
Product or component type	Wall plate
Device application	Control

#### Complementary

Colour	Cover plate: pure white Grid: black
Provided equipment	Mounting plate Flying lead
Control type	5 x push-button dual-action
Local signalling	Status: LED (tri-colour) on push-button
Switch application	Lighting Timer Audio Blind control Fan speed control Scene control On/Off switching Shutter control Dimming up/down control Page navigation
Local display	Backlit LCD display
Display type	Colour TFT display
Display size	2.8 inch
Messages display capacity	Up to 4 pages
Information displayed	Load type Temperature Power Date Time Operating mode
Number of outputs	16 in 4 page option 5 in 1 page option
Function of module	Proximity sensor monitoring wake-up
Communication port protocol	C-Bus - 2 wires
[Us] rated supply voltage	15...36 V: DC
Maximum supply current	32 mA
Material	Glass
Connector type	Mini USB port (rear) Socket (rear) for C-Bus
Function available	Firmware update by USB

User language	Multi-language
Product compatibility	LAN cable Cat. 5e
Electrical connection	Flying lead
Clamping connection capacity	0.2...1.5 mm <sup>2</sup>
Fixing mode	By screws
Mounting support	Wall
Width	77 mm
Height	123 mm
Depth	35 mm
Embedding depth	23.5 mm
Colour code	PW

## Environment

IP degree of protection	IP20
Ambient air temperature for operation	5...45 °C
Product certifications	CE[RETURN]RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	11 cm
Package 1 Length	15.5 cm
Package 1 Weight	306 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	20.6 cm
Package 2 Width	22.5 cm
Package 2 Length	33 cm
Package 2 Weight	2.903 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	240
Package 3 Height	103 cm
Package 3 Width	66 cm
Package 3 Length	67.5 cm
Package 3 Weight	97.082 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins