

Product data sheet

Characteristics

5100P24/2700AU

C-Bus Control and Management System,
 Power Supply Suits C-Bus Control and
 Management System, 6.4" Colour Touch
 Screen Controller, 24VDC, 65W



Main

Range	Standard Series
Product brand	Clipsal
Product or component type	Power supply
Device application	Power supply

Complementary

Power consumption in VA	63 VA
Rated power in W	63 W
Supply voltage limits	100...240 V
Supply circuit type	AC
Network frequency	50 Hz 60 Hz
Secondary voltage	24 V DC (adjustable)
Maximum output current	2.7 A
Protection type	Against short-circuits
Function of module	With output voltage stabilized
Width	115.5 mm
Height	51 mm
Depth	33 mm

Environment




IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.06 cm
Package 1 Width	0.164 cm
Package 1 Length	0.236 cm
Package 1 Weight	688 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes