

Product data sheet

Characteristics

5100P24/2700AU

Power Supply, C-Bus Control and Management System, Suits 6.4" Colour Touch Screen Controller, 24VDC, 65W



Main

Range	Standard Series
Product brand	Clipsal
Product or component type	Power supply
Device application	Power supply

Complementary

Power consumption in VA	63 VA
Rated power in W	63 W
Supply voltage limits	100...240 V
Supply circuit type	AC
Network frequency	50 Hz 60 Hz
Secondary voltage	24 V DC (adjustable)
Maximum output current	2.7 A
Protection type	Against short-circuits
Function of module	With output voltage stabilized
Width	115.5 mm
Height	51 mm
Depth	33 mm




Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.06 cm
Package 1 Width	0.164 cm
Package 1 Length	0.236 cm
Package 1 Weight	688 g

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes