

Product data sheet

Characteristics

5500PCU

C-Bus Control and Management System, Pc Interface Housed in A 4M, Din Rail Enclosure, USB



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Interface module
Device application	Connection

Complementary

Number of modules	4
Communication port protocol	USB
Communication port support	USB
Transmission rate	9600 bauds
Mounting support	DIN rail
Local signalling	LED







Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.2 cm
Package 1 Width	12.7 cm
Package 1 Length	16.5 cm
Package 1 Weight	286.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	22.0 cm
Package 2 Width	30.0 cm
Package 2 Length	43.5 cm
Package 2 Weight	3.285 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240
Package 3 Height	80.0 cm
Package 3 Width	120.0 cm
Package 3 Length	110.0 cm
Package 3 Weight	87.84 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins