

## Product data sheet

### Characteristics

# 4RC240SIS300

Residual current circuit breaker, MAX4, 2P, 40 A, 300 mA, type A-SI, 240 V



### Main

Range	MAX4
Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	40 A
Earth-leakage sensitivity	300 mA
Earth-leakage protection class	Type A-SI (Super Immunised)

### Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	6 kV
Mounting support	DIN rail
Size	81 x 72 x 75 mm conforming to DIN 43880
Trip unit protection functions	Selective protection

### Environment

Standards	AS/NZS 61008
IP degree of protection	IP40
Pollution degree	2
Ambient air temperature for operation	-5...40 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.18 kg
Package 1 Height	0.92 dm
Package 1 width	0.38 dm
Package 1 Length	0.84 dm

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>