

Product data sheet

Characteristics

56C315ELP-RO

Clipsal - 56 Series, RCD Protected Portable Socket Outlet, 250V, 15A, 3 Flat PIN, IP66



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Orange (RAL 2004)

Complementary

Number of poles	3
Control type	Push-button
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz
Network number of phases	1 phase
Number of gangs	4 gangs
Installation direction	Vertical
Material	PC + PET
Electrical connection	Power cord
Depth	105 mm
Width	195 mm
Height	243 mm
Net weight	2.64 kg
Targeted country	Australia

Environment



Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66
Earth-leakage protection class	Class A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	26 cm
Package 1 Width	11.5 cm
Package 1 Length	40 cm
Package 1 Weight	2.64 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Height	40.8 cm

Package 2 Width	35 cm
Package 2 Length	48.6 cm
Package 2 Weight	5280 g
Unit Type of Package 3	PAL
Number of Units in Package 3	24
Package 3 Height	96.6 cm
Package 3 Width	116.5 cm
Package 3 Length	116.5 cm
Package 3 Weight	97360 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes