

## Product data sheet

### Characteristics

# 56C315ELP-RO

56 Series switched socket IP66 portable RCD 3 pin 15 A - Restance Orange



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Orange (RAL 2004)

### Complementary

Number of poles	3
Control type	Push-button
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz
Network number of phases	1 phase
Number of gangs	4 gangs
Installation direction	Vertical
Material	PC + PET
Electrical connection	Power cord
Depth	105 mm
Width	195 mm
Height	243 mm
Net weight	2.64 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.64 kg
Package 1 Height	26 cm
Package 1 width	11.5 cm
Package 1 Length	40 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	2
Package 2 Weight	5280.0 g
Package 2 Height	40.8 cm

Package 2 width	35 cm
Package 2 Length	48.6 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	24
Package 3 Weight	97360.0 g
Package 3 Height	96.6 cm
Package 3 width	116.5 cm
Package 3 Length	116.5 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>