

## Product data sheet

### Characteristics

# 56C315RC-GY

## 56 Series switched socket surface IP66 RCD 3 pin 15 A - Grey



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

### Complementary

Number of poles	3
Control type	Push-button
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Installation direction	Vertical
Device mounting	Surface
Material	Polycarbonate
Connections - terminals	Screw terminals cable(s) 1...6 mm <sup>2</sup>
Depth	102 mm
Width	101 mm
Height	204 mm
Net weight	0.96 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.006 kg
Package 1 Height	11.6 cm
Package 1 width	10.8 cm
Package 1 Length	20.8 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>