

Product data sheet

Characteristics

56C510RC-GY

Switched Socket, Clipsal - 56 Series, RCD

Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Control type	Push-button
[In] rated current	10 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	3 gangs
Installation direction	Vertical
Material	Polycarbonate
Connections - terminals	Screw terminal cable(s) 1.5...16 mm ²
Mounting mode	Surface mounted
Depth	110 mm
Width	101 mm
Height	294 mm
Net weight	1.748 kg
Targeted country	Australia

Environment




Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66
Earth-leakage protection class	Class A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	10.1 cm
Package 1 Length	30.0 cm
Package 1 Weight	1.748 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	30.0 cm
Package 2 Width	23.0 cm

Package 2 Length	37.0 cm
Package 2 Weight	10.0 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Take-back	No