

Product data sheet

Characteristics

4RCBM220/30

Residual current breaker with overcurrent protection (RCBO), MAX4, 2P, 20 A, C curve, 10000 A, 240 V, 30 mA, AC type



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	20 A
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type AC
Breaking capacity	10000 A

Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

Packing Units

Package 1 Weight	224.000 g
Package 1 Height	40.000 mm
Package 1 width	82.000 mm
Package 1 Length	97.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free plastic parts product