

Product data sheet

Characteristics

5031NMS

Push button interface, C-Bus, 30 Series module, slave



Main

Range	C-Bus
Product brand	Clipsal
Product name	Series 30M
Product or component type	Push-button interface
Device application	Control
Colour	White
Switch application	Load switching Dimming up/down control Timer Scene control Bell switch Shutter control Fan speed control Blind control

Complementary

Range compatibility	C-Bus Iconic wall plate
Dimmer control	255 possible levels
Device mounting	Wall mounted by Series 30M grid
[Ue] rated operational voltage	15...36 V DC
Input impedance	100 kOhm at 1 kHz
Local signalling	LED (blue/orange)status:
Suitable cable type	Twisted unshielded pairs cable category 5e
Isolation voltage	3.75 kV from C-Bus to mains
Communication network type	C-Bus via 30 series master module
Module type	Slave
Control type	Push-button
Depth	20 mm
Width	23 mm
Height	23 mm
Net weight	0.007 kg
Material	Plastic
Starting time	5 s
Module configuration	Programmed with learn mode Programmed with C-Bus software
Time delay range	1s...18h12m15s
Current consumption	18 mA

Environment


Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 % non-condensing
Product certifications	RCM
Standards	AS/NZS CISPR 15 AS/NZS CISPR 14-1 AS/NZS 60669.2.1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Weight	10.000 g
Package 1 Height	25.000 mm
Package 1 width	40.000 mm
Package 1 Length	130.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	 End Of Life Information