

Product data sheet

Characteristics

56K2SW120-GY

Clipsal - 56 Series, Switches, Key Operated Surface Switches - IP66, 250V 20A - Single Pole



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

Complementary

Switch function	1-pole
Poles description	1P
[Icm] rated short-circuit making capacity	1 kA
Control type	Rotary knob
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	20 A
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	112 mm
Net weight	0.596 kg
Breaking capacity	20 kA
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Actuator	Key
[Icw] rated short-time withstand current	1.2 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV
Motor M-rating AS3133	M250 at 250 V

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.25 cm
Package 1 Width	11.25 cm
Package 1 Length	10.65 cm
Package 1 Weight	587.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	25.0 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	7.152 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile