

Product data sheet

Characteristics

56K2SW120PWD-GY

56K2SW120 TO SUIT PWD



Main

Range of product	Series 56
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	1-pole
[Icm] rated short-circuit making capacity	1 kA
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A
Marking	ON-OFF
Marking location	Marking on surface
Actuator	Key
[Icw] rated short-time withstand current	1.2 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV


Environment

Standards	AS/NZS 3123 AS/NZS 3947-3
-----------	------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins