

Product data sheet

Characteristics

56C320FLE-GY

56 Series Switched Socket Outlet- 20A- 3 Pin- 1P- 250V - Less Enclosure - Grey



Main

Range	Clipsal - 56 Series
Product or component type	Switched socket
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand
Plug, socket, control station shape	Angled Straight
[In] rated current	20 A
[Ue] rated operational voltage	250 V AC 50 Hz
Poles description	1P + N + E
Protection type	Without protection
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminal cable(s) 2.5...6 mm ²
Mounting mode	Surface mounted
Outlet standard	Industrial
Depth	72 mm
Width	101 mm
Height	204 mm
Net weight	1.2 kg
Targeted country	Australia

Environment

Standards	AS/NZS 3123
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Package 1 Weight	1.000 kg
------------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile