

Product data sheet

Characteristics

56K2SW320PWD-GY

56 Series - Switch - Keylock - 3 Pole - 20A - 500V - grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

Complementary

Switch function	3-pole
Poles description	3P
[Icm] rated short-circuit making capacity	1 kA
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	20 A
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	112 mm
Product weight	1 kg
Breaking capacity	20 kA
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Actuator	Key
[Icw] rated short-time withstand current	1.2 kA for 1 s
[Uimp] rated impulse withstand voltage	4 kV
Motor M-rating AS3133	M200 at 500 V

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	612.6 g
Package 1 Height	11.3 cm
Package 1 width	10.5 cm
Package 1 Length	10.7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile