

Product data sheet

Characteristics

56CV532-GY

Switched Socket Outlet, Clipsal - 56 Series, 500V, 32A, 5 Round PIN, IP66, 3 Pole, Vertical

Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	5
Plug, socket category	Low voltage
Outlet standard deviation	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	32 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + N + E
Protection type	Without protection
Device mounting	Surface
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 4...16 mm ²
Electrical connection	Industrial connector
Depth	108 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3123 AS/NZS 3133
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.3 cm
Package 1 Width	11.5 cm
Package 1 Length	20.6 cm

Package 1 Weight	970 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	11640 g
Unit Type of Package 3	PAL
Number of Units in Package 3	480
Package 3 Height	120 cm
Package 3 Width	116.5 cm
Package 3 Length	116.5 cm
Package 3 Weight	499600 g

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Take-back	No