

## Product data sheet

### Characteristics

# 56DB4L-GY

## 56 Series Adaptable Enclosure - 4 Gang - Lid - Grey



### Main

|                           |                     |
|---------------------------|---------------------|
| Range                     | Clipsal - 56 Series |
| Range of product          | Series 56           |
| Product brand             | Clipsal             |
| Product or component type | DIN cover           |
| Colour                    | Grey (RAL 7035)     |

### Complementary

|                 |                        |
|-----------------|------------------------|
| Material        | Polycarbonate: housing |
| Device mounting | Surface                |
| Mounting mode   | Wall-mounted           |
| Width           | 192 mm                 |
| Height          | 192 mm                 |
| Depth           | 78 mm                  |
| Net weight      | 0.42 kg                |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Standards                             | AS 3100                     |
| IP degree of protection               | IP66 conforming to AS 60529 |
| Ambient air temperature for operation | -25...75 °C                 |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 21.1 cm  |
| Package 1 Width              | 10.4 cm  |
| Package 1 Length             | 20.3 cm  |
| Package 1 Weight             | 481.0 g  |
| Unit Type of Package 2       | CAR      |
| Number of Units in Package 2 | 6        |
| Package 2 Height             | 21.0 cm  |
| Package 2 Width              | 34.8 cm  |
| Package 2 Length             | 44.5 cm  |
| Package 2 Weight             | 3.275 kg |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |