

Product data sheet

Characteristics

56DOL12/1B-GY

Direct Online Starter, Clipsal - 56 Series, 3Ph
5.5Kw 240V

Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: grey

Complementary

Colour code	GY
Motor starter type	Direct on line
Control type	Push-button
[Us] rated supply voltage	240 V AC 50 Hz
Network type	AC
Rated operational power in W	5.5 kW at 240 V (AC-3)
[Ie] rated operational current	12 A
Overload current	9...13 A
Connections - terminals	Screw terminal solid Screw terminal stranded
Tightening torque	0.8 N.m
Network number of phases	3 phases
Product destination	2 push-button
Height	204 mm
Width	101 mm
Net weight	1.44 kg
Targeted country	Australia
Market segment	Utility Small commercial Industry



Environment

Suitability for isolation	No
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3100 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.44 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes