

Product data sheet

Characteristics

56ES1-CG

56 Series Enclosure - 1 Gang - Shallow - 2 x 25mm - 1 x 32mm conduit entries



Main

| | |
|------------------|---------------------|
| Range of product | Series 56 |
| Range | Clipsal - 56 Series |
| Product brand | Clipsal |
| Colour | Dark grey |

Complementary

| | |
|--------------------------|-----------------------------------|
| Number of gangs | 1 gang |
| Device mounting | Surface |
| Mounting mode | Wall-mounted |
| Cable entry number | 2 |
| Material | PVC (polyvinyl chloride): housing |
| Number of mounting holes | 4 |
| Length | 38 mm |
| Width | 102 mm |
| Depth | 40 mm |
| Height | 102 mm |
| Net weight | 0.78 kg |
| IP degree of protection | IP66 conforming to AS 60529 |
| Standards | AS 3100 |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...75 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.8 cm |
| Package 1 Width | 10.15 cm |
| Package 1 Length | 10.15 cm |
| Package 1 Weight | 180 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 2 |
| Package 2 Height | 10.1 cm |
| Package 2 Width | 10.6 cm |
| Package 2 Length | 10.5 cm |
| Package 2 Weight | 0.394 kg |
| Unit Type of Package 3 | CAR |

| | |
|------------------------------|---------|
| Number of Units in Package 3 | 48 |
| Package 3 Height | 21 cm |
| Package 3 Width | 34.8 cm |
| Package 3 Length | 44.5 cm |
| Package 3 Weight | 9.9 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |