

Product data sheet

Characteristics

56SO550G

Clipsal - 56 Series, Internal Socket Housings, 500V 50A - 5 Round Pins



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

Complementary

Plug, socket category	Low voltage
Device mounting	Surface
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC 50 Hz conforming to EN 60309-2
Poles description	3P + N + E
Voltage colour	Black
Duration	7 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 10...16 mm ² rigid or stranded cable
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	U
Outlet standard	Industrial
Net weight	0.001 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile