

Product data sheet

Characteristics

56SW110/I-GY

Surface Switch, Clipsal - 56 Series, 1 Gang, 250VAC, 10A, Intermediate



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Grey
Suitability for isolation	No
Colour	Cover: grey

Complementary

Poles description	1P
Control type	Rotary knob
Number of poles	1
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	10 A
Marking	ON-OFF
Marking location	Marking on surface
Mounting Type	By screws
Breaking capacity	10 kA
Targeted country	Australia
Height	107 mm
Width	101 mm
Depth	83 mm
Net weight	0.48 kg
Motor M-rating AS3133	M80 at 250 V
Switch function	1-pole
Rotary handle padlocking	2 padlocks 8 mm

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	10.9 cm
Package 1 Length	10.9 cm
Package 1 Weight	383.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations