

Product data sheet

Characteristics

56K2SW350-GY

Key Operated Surface Switch, Clipsal - 56 Series, IP66, 500V 50A, Triple Pole



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Grey
Suitability for isolation	Yes
Colour	Cover: grey

Complementary

Poles description	3P
Control type	Rotary knob
Number of poles	3
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	50 A
Marking	ON-OFF
Marking location	Marking on surface
Mounting Type	By screws
Breaking capacity	50 kA
Targeted country	Australia
Height	107 mm
Width	101 mm
Depth	112 mm
Net weight	0.6 kg
Actuator	Key
Motor M-rating AS3133	M200 at 500 V
Switch function	3-pole
Rotary handle padlocking	2 padlocks 8 mm

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.25 cm
Package 1 Width	11.25 cm
Package 1 Length	10.65 cm
Package 1 Weight	702.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	250 mm
Package 2 Width	214 mm
Package 2 Length	338 mm
Package 2 Weight	8.43 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	768
Package 3 Weight	460.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations